

MOTIP Deco Clear Lacquer

Technical Information



High quality clear lacquer to treat surfaces, treated and untreated, of wood, metal, aluminium, glass, stone, and various types of plastic.

Ord.-no: 01603, 01654, 021603, 021654, 591603, 591654

Quality & properties

- Lasting Gloss
- Excellent filling property.
- Scratch free and shock proof.
- Resistant to petrol, chemicals and weather influences
- Corrosion preventive
- Excellent adhesion

Physical & chemical data

- Base: Alkyd resin
- Colourname: transparent
- Degree of gloss:
 - high gloss, >85
 - semi mat, 25 ±5
- Efficiency:
 - 400 ML – 1,25 - 1,75 m²
 - 150 ML – 0,5 m²
- Dust dry: 30 min
- Dry to touch: 3 - 4 h
- Completely dry: 24 h
- Overcoatable: 24 h
- Surfaces: wood, metal, aluminium, glass, stone and various types of plastic
- Minimum Working Temperature: 15 °C
- Maximum Working Temperature: 25 °C
- Flash point:
 - n.a.
 - 24 °C
 - 24
- Temperature resistance: 110 °C
- Content:
 - 400 ML
 - 150 ML
 - 100 ML

How to use

The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface.

The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 15 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.

Apply the clear lacquer in several thin layers. Before applying the next layer, again shake the aerosol.

Apply the clear lacquer in several thin layers. Before applying the next layer, again shake the aerosol

After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

As of August 4, 2025 – This release replaces all eventually earlier issued versions.